
Flo Split Desk Clamp

DYN/013/AS09




Reposition clamp plate (if required) to suit worksurface thickness (for desks with screens follow step 4 first)




1b

Fit clamp plate to bracket using hole position to suit required desk thickness




2

Fit M10 screw to clamp plate with clamp pad in position




3

Fit clamp to worksurface. Ensure back of the clamp is flush against edge of the worksurface




4

Tighten M10 clamp screw




Reconfiguring the 180° stop function

The Flo clamp base is factory fitted with a 180° stop feature. You can permit 360° rotation by simply pulling the cover and base from the clamp and repositioning the stop feature as shown






360° rotation configuration





180° rotation configuration



A WARNING

- Do not use this product for any purpose other than that for which it was designed
- Ensure desk/worksurface is suitable to take the weight of the arm/s and monitors
- Supported weight must not exceed the maxium load per arm
- Take care when installing as fingers could become trapped

A MAINTENANCE AND INSPECTION

- Ensure all screws are tightened and occasionally adjust if needed
- Ensure arm is pushed fully down onto the clamp before installing the monitor(s)
- Clean with a damp cloth, NO solvents

A DISCLAIMERS

- The use of power tools, lever bars or excessive force during the installation, or re-configuration of the product will invalidate your guarantee
- Failure to observe the recommendations in the use, and configuration of these products may affect your guarantee
- As a part of Colebrook Bosson Saunders ongoing product improvement programme the design of products may change without prior notice and details may vary from those illustrated

PATENTS

Colebrook Bosson Saunders hold a number of patents and other intellectual property rights covering our products and processes.

You can find patent information on our website at:

www.colebrookbossonsaunders.com/patents

Please consider leaving these instructions with the product if further installation may be required by others

DYN-013-AS09-INST-C OCT2018

FOLD



FOLD

FOLD FOLD FOLD Print size - A4 297mm x 210mm